



XENTRITE™

DESICCANT DRYING TABLET

Natural Gas drying at low pressures and low flow rates can be very difficult. Most conventional salt-type desiccants are not able to adequately dry gas under low pressures (<75 psi) or when stringent pipeline specifications (<7 lbs./mmscf) must be met.

Xentrite™ was developed to meet dew points where other desiccants and glycols cannot.

Xentrite™ can be used by itself or in combination with other desiccants such as **CD 50** and **LD 45**. In these applications, the gas flows through the **CD 50** or **LD 45** first removing most of the moisture and then through the **Xentrite** to further reduce the dew point.



7 LB/MMCF
ATTAINABLE AT
50 PSI & 60°F

20 LB/MMCF
ATTAINABLE AT
25 PSI AND 80°F

CONVENIENT
PACKAGING.

SMALL
FOOTPRINT

INTERRACHEM, LLC

PO Box 727
Newburgh, IN 47629

www.interrachem.com